



RECHARGEABLE DUAL MOUNTING MAGNIFYING WORK LIGHT 6 SMD LED

MODEL NO: **WL63/8D**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instruction manual

1. SAFETY

- ✓ Inspect the cable and connector for wear and damage to ensure items are safe before connecting to the power supply. If worn or damaged **DO NOT** use.
- ✓ Ensure the lamp is fully charged before initial use.
- ✗ **DO NOT** charge in damp conditions.
- ✗ **DO NOT** turn the lamp on when it is being charged.
- ✗ **DO NOT** shine directly into your, another person's or an animal's eyes.
- ✗ **DO NOT** allow children to use the lamp.
- ✗ **DO NOT** handle or move the lamp whilst it is being charged.
- ✗ **DO NOT** use the lamp if you suspect that the battery or the lamp casing is damaged.
- ✗ **DO NOT** leave battery in a discharged state, recharge battery immediately. Before storage, fully recharge the battery, subsequently recharge the battery at least once every six months of non-use.
- ✗ **DO NOT** attempt to open, disassemble, modify or service the battery pack.
- ✗ **DO NOT** crush, puncture, short external contacts or dispose of in fire or water.
- ✗ **DO NOT** expose to temperatures above 40°C (104°F).

2. INTRODUCTION



Powerful three dioptr 109mm & eight dioptr 24mm precision lens gives high quality magnifying capabilities. Features six SMD LEDs producing up to 60 lumens to illuminate the object for improved detailed work. Built-in touch sensitive dimmer switch. Magnifier can detach from its sturdy base and spring clamp to a work bench up to 45mm thick. Ideal for electrical engineers, engravers and fine detail work. Rechargeable 400mAh lithium cell battery. Supplied with USB cable.

3. SPECIFICATION

Model no: WL63/8D
 Battery:400mAh
 Power:.....0.5W
 Lamp voltage:5V DC
 LEDs: 6 SMD LED
 Lumen output: 60lm
 Net weight:.....380gm

4. OPERATION

- 4.1. CHARGING:**
- 4.1.1. Connect the micro-USB lead to the socket on the side of the base of the lamp (fig.1). Plug into USB power supply and turn on.
 - 4.1.2. While lamp is charging there is a red LED shining through the desk clamp surface just above the touch sensitive switch.
 - 4.2. Direct the lens away from your eyes before switching on.
 - 4.3. Lightly tap the touch pad switch on the base to turn the lamp on. Lightly tap the touch pad switch again to turn off.
 - 4.4. To modify the lamp output, press and hold the touch pad switch to dim or increase the light output.
 - 4.5. The lamp may be either desk mounted or attached to any desk/bench edge up to 40mm thick by exposing the clamp after removing the base plate.



WEEE REGULATIONS

Dispose of this product at the end of its working life in compliance with the EU Directive on Waste Electrical and Electronic Equipment (WEEE). When the product is no longer required, it must be disposed of in an environmentally protective way. Contact your local solid waste authority for recycling information.



BATTERY REMOVAL

Under the Waste Batteries and Accumulators Regulations 2009, Jack Sealey Ltd are required to inform potential purchasers of products containing batteries (as defined within these regulations), that they are registered with Valpak's registered compliance scheme. Jack Sealey Ltd's Batteries Producer Registration Number (BPRN) is BPRN00705.



ENVIRONMENT PROTECTION

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.

Note: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: Guarantee is 12 months from purchase date, proof of which is required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk