

Pre-Shipment Inspection Statement Sheet

发货前检验声明表

This form must be completed and sent to preshipment@sealey.co.uk prior to shipment of the goods for approval. Production of this product must be as per the Product Information Pack found on the Sealey SharePoint site. Failure to comply with this procedure could result in the delivery being rejected.

请在发货之前（留出足够时间提前量）填好此表发到 preshipment@sealey.co.uk 并得到确认才能发货。生产加工要按照 Sharepoint 上提供的产品包装信息。不按要求执行此操作可能导致拒收

To be completed by Supplier

Sealey Model Number	型号	SA813
Factory Model Number	工厂型号	HL-GA10
Sealey Purchase Order Number	订单号	054651
Sealey Product Description	描述	AIR HOSE REEL 10m
Order Quantity	订单数量	300
Agent/Factory	贸易公司/工厂	AVITEC
Gross Weight (kg)	毛重	3.70KG
Quantity of order tested	检验数量	300
Factory Pre-Shipment testing details	验货细节	
Comments	注解说明	

All applicable artwork, instructions, parts list and declaration of conformity match the documents provided via the Sealey SharePoint site at time of manufacture (Please select Yes or No)

所有涉及的彩盒，标贴，说明书，零备件清单，符合声明均与生产期间的 SEALEY 公司 SharePoint 网站上提供的文件相同。请选择是或否

Yes ☒ No ☐

If you cannot access SharePoint or require a new link, please contact productinfo@sealey.co.uk and

如果你无法进入 SharePoint 或者需要一个新的邮箱链接，请联系 productinfo@sealey.co.uk 获取

Complete for Electrical Items			供电子电器产品填写		
Plug fitted	插头式样	Adaptor Plug Charger	Fuse fitted	保险丝	Please select
Batch number/Date of manufacture		批次号/生产日期			
ASTA or KITEMARK number on plug					
插头上显示的 ASTA 或者 KITEMARK 的号码					
Power lead/cable number (eg. VDE H05VV-F 2x1.0mm ²)					
电线规格(例如 VDE H05VV-F 2x1.0mm ²)					
Name of manufacturer on power lead/cable					
电线上生产厂商名字					

RoHS(Hexavalent Chromium)compliant? (Select Yes/No)

ROHS(6价铬)测试否? 选择 Yes 或者 No

Yes



No



Please ensure the images are clear and can be easily read

发送前请确保照片清晰可以被辨认

Picture of Plug (showing ASTA or KITEMARK number)	Picture of Lead (showing number e.g. H05VV-F 2x1.0mm ²)
插头照片(可看清 ASTA 或者 KITEMARK 标志)	电线照片(显示线规, 例如 H05VV-F 2x1.0mm ²)
Picture of Lead (showing manufacturer name)	电线照片(显示生产商)

Complete for Trolley Jacks		供千斤顶类产品填写	
Number of units tested to 100%	100% 额载测试数量		
Tested pressure release valve	测试了安全阀		
Year of manufacture	生产年份		
Maximum saddle height (mm)	托盘最高高度		
Minimum saddle height (mm)	托盘最低高度		
Recorded descent at 100% load (m/s)	记录额载慢降速度		
100% Visual Inspection (Welds/finish/structure)	100% 目测检验(焊缝, 喷涂, 结构等)(选择是否)	Yes	No
Product is fitted with descent control? (click yes/no)	产品有无慢降(选择是否)	Yes	No

Complete for Axle Stands	供千斤顶支架填写
(References to images below)	参考以下照片

Third party testing standard	第三方测试标准			
Other testing standard	其他测试标准			
Tick to confirm the order is manufactured to the above standard		选择确认订单是按照上述标准生产		
Complete order tested to 100% SWL		产品做 100% 额载测试		
Engagement head test(Tick to confirm)	齿条顶头左右两点额载测试, 请选择确认	Qty tested	测试数量	
Test to 100% SWL (Tick to confirm)	100% 载荷测试, 请选择确认	Qty tested	测试数量	
100% Visual inspection (welds/finish/structure)	100% 外观检查(焊缝/表面/结构)	Qty tested	测试数量	
Rated capacity (single stand) (kg)	名义载荷(每只支架)(kg)			
Number of feet on stand	每只支架的脚数			
Fig. 1. Engagement head overall working area (mm2)	如图1: 齿条顶头工作面积			
Fig. 2. Engagement head plan area mm2	如图2: 齿条顶头整体投影面积			
Fig. 3. Upper column outer diameter (mm2)	如图3: 齿条外径			
Fig. 4. Distance from engagement head to wall (mm)	如图4: (支架脚蹠外缘到离得最近的支架齿条顶头最边缘距离 - H)			
Fig. 5. Max height - Base to engagement head at highest point mm	如图5: 基面到支架顶头最高点高度 - V			
Fig. 6. Height after 100% load test- Test 1	如图 6:100% 载荷测试后高度-测试 1			
Fig. 6. Height after 100% load test- Test 2	如图 6:100% 载荷测试后高度-测试 2			
Fig. 6. Height after 100% load test- Test 3	如图 6:100% 载荷测试后高度-测试 3			
Fig. 7. True area of one foot in cm2	如图 7 : 一只脚板的真实面积 (cm2)			
Fig. 8. Column engagement mm	如图 8: 最高位时上面齿条和下面支撑部分重叠的长度			

Fig. 1	如图 1	Fig. 2	如图 2	Fig. 3	如图 3

Fig. 4

如图 4




Fig. 5

如图 5




Fig. 6

如图 6




Fig. 7

如图 7





Fig. 8

如图 8



Product/Document Images (Complete for all products)	产品和包材图片(适用所有产品)
Please ensure the images are clear and can be easily read	发送前请确保照片清晰可以被辨认

Picture of product

产品照片



Picture of product

产品照片



Picture of product

产品照片



Artwork label

彩盒彩稿标贴照片



Artwork label

彩盒彩稿标贴照片



Artwork label

彩盒彩稿标贴照片



Batch Number

批次号



Artwork label

彩盒彩稿标贴照片



Artwork label

彩盒彩稿标贴照片




Please ensure the images are clear and can be easily read

发送前请确保照片清晰可以被辨认


Artwork label

彩盒彩稿标贴照片




Artwork label

彩盒彩稿标贴照片



Artwork label

彩盒彩稿标贴照片



UK Energy Document


英国能效贴

EU Energy Document

欧盟能效贴


Sealey Thank You Card

感谢卡




Instructions issue no./date

说明书右下角版本号 and 日期近照



Date on declaration of conformity

符合声明日期近照



Parts list issue no./date

零备件清单右下角版本号 and 日期近照




Please ensure the images are clear and can be easily read

发送前请确保照片清晰可以被辨认

Picture of Sealey barcode

条码照片



Picture of packaging studio code

彩盒彩贴条码附近的 6 位 Studio 代码近照




Picture of Sealey packaging

SEALEY 产品包装照片




Outer carton shipping Marks

外箱唛头



Outer carton weight/barcode label

外箱唛头显示的重量和条码标贴上显示重量



Picture of outer carton Sealey logo

外箱的 SEALEY logo 一面的照片



Picture of Inner Packaging

内包装照片



Picture of Inner Packaging

内包装照片



Picture of Inner Packaging

内包装照片